


Céliane™
Connected wireless control for roller shutters

Cat. Nos: 0 676 46/47 - 0 648 97



## 1. USE

Zone or centralised control for wired roller shutter switches.


- Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

Can control up to 20 roller shutter switches.

## 2. RANGE


Description	White	Titanium	Graphite
Connected wireless control for roller shutters. Supplied complete with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	0 676 46	0 676 47	0 648 97

# 3. DIMENSIONS (mm)



Cat. Nos.	Α	В	D
0 676 46/47 - 0 648 97	82	90	13

## 4. OPERATION



## 5. TECHNICAL CHARACTERISTICS

# ■ 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids:

- IP 20 without plate and rocker plate
- IP 40 for assembled product

# ■ 5.2 Material characteristics

Colour	White	Titanium	Graphite
Plate	ABS + PC	ABS + Metal	ABS + Metal
Rocker plate	ABS	Painted ABS	Painted ABS

Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free UV resistant

Self-extinguishing:  $650^{\circ}\text{C}/30 \text{ s}$ 

#### ■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day

**ZigBee radio technology** frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN)

# ■ 5.4 Climate characteristics

Usage temperature: +5°C to +45°C Storage temperature: 0°C to +45°C

# Céliane™

# **Connected wireless control for roller shutters**

# Cat. Nos: 0 676 46/47 - 0 648 97

# 6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

## 7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

Replacement rocker plate: 0 648 19: White 0 648 29: Titanium

0 648 29: Titanium 0 648 39: Graphite

## 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 676 46/47 - 0 648 97) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com

Created: 16/01/2018 **La legrand** 

Technical data sheet: F02506EN/00 Updated: 25/07/2018